



DCF899B

20V MAX* XR® HIGH TORQUE 1/2 IN. IMPACT WRENCH WITH DETENT PIN ANVIL (TOOL ONLY)

- Up to 700 ft-lbs of max torque and 1200 ft-lbs of max breakaway torque
- Compact design of 8-13/16 in. in length
- Multi-speed control for a variety of applications



*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

**NO LOAD
SPEED (RPM)**
0-400/1200/1900

MAX TORQUE
700 LBF/FT

**IMPACT RATE
PER MINUTE**
0-2400

Includes: (1) DCF899 1/2 in. Impact Wrench

© 2022 DEWALT

ICDCF899BFT