



Main

Range	I-Line
-------	--------

Complementary

Main Type	Main lugs
Width	35.47 in (900.94 mm)
Height	48 in (1219.20 mm)
Product Destination	Panelboard interior HCP 42 in (1066.80 mm) 68 in (1727.20 mm)
Rated Current	1200 A
Mounting Space	63 in (1600.20 mm)
Net Weight	259.99 lb(US) (117.93 kg)

Ordering and shipping details

Category	00016 - I-LINE PB RTA
Discount Schedule	PE1A
GTIN	00785901932819
Nbr. of units in pkg.	1
Package weight(Lbs)	206 lb(US) (93.44 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.79 ft (0.241 m)
Package 1 width	3.18 ft (0.970 m)
Package 1 Length	4.25 ft (1.295 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure

 [Product Environmental Profile](#)

PVC free

Yes

Contractual warranty

Warranty

18 months
