

9422ATCF332

Operating mechanism, flange mounted, variable depth, 30A, 600 V, fuseholder, switch mechanism, 6 inch handle, NEMA 4X



Main

| | |
|-----------------|---------------------------|
| Range | 9422T |
| Product | Disconnect Switch |
| Disconnect Type | Fusible disconnect switch |

Complementary

| | |
|-------------------|---|
| Mounting Type | Flange rod variable depth |
| Current Rating | 30 A |
| Horsepower Rating | 7.5 Hp 200 V AC 7.5 Hp 230 V AC 15 Hp 460 V AC 20 Hp 575 V AC 5 hp 250 V DC |
| Fuse Rating | 60 A 250 V 30 A 600 V |
| Handle Type | 6 in handle included NEMA 4/4X enclosures Stainless Steel |
| Fuse Type | H J K R |

Environment

| | |
|----------------|----------------------|
| Certifications | CSA UL Recognized |
|----------------|----------------------|

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 21732 - 9422 |
| Discount Schedule | CP1 |
| GTIN | 00785901316428 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 8.92 lb(US) (4.05 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 6.90 in (17.526 cm) |
| Package 1 width | 11.30 in (28.702 cm) |
| Package 1 Length | 16.00 in (40.640 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|