



Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	60 A
[Ue] rated operational voltage	<= 600 V AC/DC
Fuse type	R
Fuse size	1.0625 x 5.5 in
Number of poles	3
Electrical connection	Box lugs
Wire Gauge	AWG 14...AWG 2 copper or aluminium
SCCR	200 kA UL 512
Product certifications	UL listed file E40747 CCN IZLT CE CSA file 70360 class 6225 01
Operating Temperature	-40...302 °F (-40...150 °C)
Mounting Type	Surface mount
Block Material	Phenolic block
Wire stripping length	0.5625 in (14.29 mm)
Terminal Tightening Torque	Lugs 50 lbf.in (5.65 N.m) AWG 3...AWG 2 copper or aluminium Lugs 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium Lugs 40 lbf.in (4.52 N.m) AWG 8 copper or aluminium Lugs 35 lbf.in (3.95 N.m) AWG 12...AWG10 copper or aluminium Lugs 35 lbf.in (3.95 N.m) AWG 14 copper
Height	6.75 in (171.45 mm)
Width	5.08 in (129.03 mm)
Depth	2.12 in (53.85 mm)

Ordering and shipping details

Category	21701 - 9080 FB
Discount Schedule	CP1
GTIN	00785901097259
Nbr. of units in pkg.	1
Package weight(Lbs)	1.4 lb(US) (0.64 kg)
Returnability	Yes
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.10 in (5.334 cm)
Package 1 width	5.10 in (12.954 cm)
Package 1 Length	6.80 in (17.272 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	29.50 lb(US) (13.381 kg)
Package 2 Height	7.20 in (18.288 cm)
Package 2 width	11.80 in (29.972 cm)
Package 2 Length	22.50 in (57.15 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------