

CM200S

Meter mains, QO, combination service entrance, ringed socket, 200A, surface mount, no bypass



Main

Product or component type	Meter Mains
Range of product	QO

Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Network number of phases	1
Meter socket type	Ringed
Mounting	Surface
Number of spaces	0
Number of circuits	0
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 4...250 kcmil aluminium/copper)line side AWG 8...AWG 2/0 2 aluminium/copper)service ground
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service feed location	OH UG
Bypass type	No bypass
Height	18.23 in (463.04 mm)
Width	19.58 in (497.33 mm)
Depth	4.37 in (111.00 mm)

Environment

Product certifications	UL E-6294
------------------------	-----------

Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901291763
Nbr. of units in pkg.	1
Package weight(Lbs)	27.23 lb(US) (12.35 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	20.50 in (52.070 cm)
Package 1 width	5.50 in (13.970 cm)
Package 1 Length	20.20 in (51.308 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------