

# Product data sheet

## Characteristics

# UTH4213T

Individual meter socket, ringless socket, lever bypass, 4 jaws no release, OH, UG, 200 A, up to 600 VAC single phase 3W



### Main

Product or component type	Meter Socket
Meter socket type	Ringless
Hub type	A-L ACPL closing plate

### Complementary

Meter socket rated current	200 A
Number of jaws	4 with jaw release
Bypass type	Lever bypass
Phase	1 phase
[Ue] rated operational voltage	600 V AC
Enclosure material	Steel
Box number	9R
Electrical connection	Lugs 0.5" hex
Service feed location	UG OH
Wiring configuration	3-wire
Device mounting	Surface
Height	19.00 in (482.60 mm)
Width	13.00 in (330.20 mm)
Depth	4.94 in (125.48 mm)

### Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

### Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	00785901627685
Nbr. of units in pkg.	1
Package weight(Lbs)	20.93 lb(US) (9.49 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 1 Height	5.80 in (14.732 cm)
Package 1 width	13.70 in (34.798 cm)
Package 1 Length	20.50 in (52.070 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Under investigation

## Contractual warranty

Warranty	18 months
----------	-----------