



Main

| | |
|-----------------------|---------------------------|
| Product | Miniature circuit-breaker |
| Range | QO |
| Current Rating | 110 A |
| Voltage Rating | 120/240 V AC 120 V AC |
| Mounting Type | Plug-in |
| Number of Poles | 2P |
| Circuit Breaker Type | Standard |
| Ratings | HACR rated |
| Electrical Connection | Box lugs |

Complementary

| | |
|------------------------|--|
| Interrupt Rating | 22 KA 120/240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz |
| Number of Panel Spaces | 2 |
| Wire Size | AWG 4...300 kcmil copper or aluminium |
| Tightening Torque | 40.71 lbf.in (4.6 N.m) |
| Height | 3.5 in (88.90 mm) |
| Width | 1.5 in (38.10 mm) |
| Depth | 2.91 in (73.91 mm) |

Environment

| | |
|----------------|------------------|
| Certifications | UL Listed CSA |
| Ambient Rating | 104 °F (40 °C) |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 00926 - QO IND SPECIALTY CB |
| Discount Schedule | DE2A |
| GTIN | 00785901054931 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.74 lb(US) (0.34 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|--------------------|
| Package 1 Height | 1.50 in (3.810 cm) |
| Package 1 width | 3.80 in (9.652 cm) |
| Package 1 Length | 3.50 in (8.890 cm) |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|