



## Main

Product or component type	Circuit breaker
---------------------------	-----------------

## Complementary

Line Rated Current	90 A
Breaking capacity code	D
Magnetic hold current	1000 A
Trip unit technology	Thermal-magnetic
Magnetic tripping current	1800 A
Tightening torque	247.82 lbf.in (28 N.m) 0.04...0.23 in <sup>2</sup> (25...150 mm <sup>2</sup> ) (AWG 4...300 kcmil)
Height	6.47 in (164.34 mm)
Width	4.5 in (114.30 mm)
Depth	3.93 in (99.82 mm)
Continuous current rating	80 %

## Ordering and shipping details

Category	00024-Q2 & QE METERING BREAKERS
Discount Schedule	DE2A
GTIN	00785901568797
Package weight(Lbs)	3.26 lb(US) (1.480 kg)
Returnability	Yes
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free product

## Contractual warranty

---

Warranty	18 months
----------	-----------

---