



Main

Range of product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Shielded twisted pair straight cable
Accessory / separate part destination	Ethernet network
Cable length	16.40 ft (5 m)

Complementary

Transmission support medium	Twisted shielded pairs cable
Communication network category	5e
AWG gauge	AWG 24
Electrical connection	2 connectors, RJ45 straight 8
Marking	UL
Cover material	PVC

Environment

IP degree of protection	IP20
Standards	IEC 11801 class D UL 444 EN 50173 class D CMG FT4 EIA/TIA-568 category CAT 5E

Ordering and shipping details

Category	18225 - PLC NTRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	00785901321453
Nbr. of units in pkg.	1
Package weight(Lbs)	0.57 lb(US) (0.26 kg)
Returnability	No
Country of origin	TH

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	7.48 in (19 cm)
Package 1 Length	9.06 in (23 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------