



Main

| | |
|------------------------------------|--|
| Range | TeSys |
| Device short name | GS2AE |
| Product or component type | Shaft extension |
| Accessory / separate part category | Control accessory |
| Range compatibility | TeSys GS GS1D TeSys GS GS2D FuPacT GS GSB32 FuPacT GS GSC32 |
| Switch rated current | 30 A 32 A |

Complementary

| | |
|---------------------|------------------------|
| Length | 12.60 in (320 mm) |
| Shaft cross section | 5 x 5 mm |
| Net Weight | 0.28 lb(US) (0.125 kg) |

Ordering and shipping details

| | |
|-----------------------|--------------------------------|
| Category | 22640 - IEC DISCONNECT-GS1,LK3 |
| Discount Schedule | I11 |
| GTIN | 00785901126973 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.25 lb(US) (0.11 kg) |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.38 in (3.5 cm) |
| Package 1 width | 14.49 in (36.8 cm) |
| Package 1 Length | 2.20 in (5.6 cm) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 18 |
| Package 2 Weight | 5.26 lb(US) (2.386 kg) |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |

Offer Sustainability

| | |
|---------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |

| | |
|----------------------------|---|
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|