



## Main

Product Type	Load Center Cover
Marketing Trade Name	Homeline
Cover Type	Combination flush/surface cover

## Complementary

Number of Spaces	42
Surface Finish	Baked enamel grey
Height	40.57 in (1030.48 mm)
Width	15.44 in (392.18 mm)
Tightening Torque	Screw 2.3 N.m

## Ordering and shipping details

Category	00185 - MISC. HOM LOAD CENTERS
Discount Schedule	DE3C
GTIN	00785901132547
Nbr. of units in pkg.	1
Package weight(Lbs)	15.16 lb(US) (6.88 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Package 1 Height	0.11 ft (0.033 m)
Package 1 width	1.30 ft (0.396 m)
Package 1 Length	3.41 ft (1.039 m)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

---

Warranty

Lifetime

---