



Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	IMA

Complementary

Surge Current	160 kA per phase
Voltage Rating	208Y/120 V AC
Number of Phases	3 phase
Wiring Configuration	4-wire
Connection	Lugs AWG 12...AWG 2 aluminium/copper 35.40 lbf.in (4 N.m)
MCOV	150 V
Nominal Discharge Current	20 kA
SCCR	200 kA
Provided Equipment	Alarm enable/disable switch Diagnostic display Backplane Cables
Height	6.13 in (155.7 mm)
Width	9.86 in (250.4 mm)
Depth	3.65 in (92.7 mm)

Environment

Enclosure Rating	NEMA 2
Standards	UL 1449:ed. 4 CSA C22.2 No 8:1986 UL 96A:ed. 12 UL 1283 IEC 61643-1

Ordering and shipping details

Category	08468 - SURGE PROTECTION OEM
Discount Schedule	DE1B
GTIN	00785901599159
Nbr. of units in pkg.	1
Package weight(Lbs)	8.4 lb(US) (3.81 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------