

Product data sheet

Characteristics

LDB124

Wireway, Square-Duct, 12 inch by 12 inch, 4 feet long, hinged cover, N1 paint, NEMA 1



Main

Product	Straight length
Range	SQUARE-Duct
Length	4 ft (1.22 m)
Cross Section	12 x 12 in
Enclosure Rating	NEMA 1
Enclosure Material	Steel 14 gauge without knock-outs
Finish	Gray polyester powder ANSI 49
Cover Type	Hinged cover
Certifications	UL Listed CSA

Ordering and shipping details

Category	01421 - LDB WIREWAY, NEMA 1
Discount Schedule	PE9
GTIN	00785901104001
Nbr. of units in pkg.	1
Package weight(Lbs)	53 lb(US) (24.04 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	1.08 ft (0.330 m)
Package 1 width	1.08 ft (0.330 m)
Package 1 Length	4.05 ft (1.234 m)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.