



Main

Product	Circuit breaker
Range of product	Powerlink
Circuit Breaker Type	ECB-G3
Circuit breaker application	Switching Duty rated HACR rated HID rated
Options	Motor for circuit-breaker 24 V DC
Trip unit technology	Thermal-magnetic, standard, LI

Complementary

Line Rated Current	15 A
Product certifications	CSA UL Listed
Voltage Rating	480Y/277 V AC
Mounting mode	Bolt-on
Number of Poles	2P
Interrupt Rating	14 KA 480Y/277 V AC 65 kA 120/240 V AC
Number of spaces required	2
Electrical connection	Bolted connection
Wire Gauge	AWG 12...AWG 8 aluminium AWG 10...AWG 8 copper

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	09663-POWERLINK GEN-3 ECB BREAKERS
Discount Schedule	DE8A
GTIN	00785901299561
Package weight(Lbs)	2.68 lb(US) (1.216 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------