

# Product data sheet

## Characteristics

# GS2AH440

External rotary handle, TeSys GS, red handle, front mounting, 2 positions I-O, NEMA 4-4X, for GS 30-400A UL



### Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys GS GS2EU TeSys GS GS2GU TeSys GS GS2JU TeSys GS GS2MU TeSys GS GS2QU
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

### Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	30 A 60 A 100 A 200 A 400 A
Standards	CSA UL
Net Weight	0.53 lb(US) (0.24 kg)

### Environment

NEMA degree of protection	NEMA 4/4X
---------------------------	-----------

### Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901015321
Nbr. of units in pkg.	1
Package weight(Lbs)	0.57 lb(US) (0.26 kg)
Returnability	Yes
Country of origin	TN

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.36 in (6 cm)
Package 1 width	5.51 in (14 cm)
Package 1 Length	6.69 in (17 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Weight	12.13 lb(US) (5.502 kg)

Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------