

Product data sheet

Characteristics

TVS3DSPHC

TVSS accessory, display kit, 3 phase, horizontal, counter



Main

Product	Industrial digital display unit Counter module
Range	SurgeLogic SurgeLogic
Device Short Name	IMA

Complementary

Surge Current	120 kA per phase
Voltage Rating	120/240 V AC 208Y/120 V AC 480Y/277 V AC 600Y/347 V AC
Number of Phases	3 phase
Connection	RJ45 connector bottom
Local Signalling	LED green per phase normal operation Alarm error

Ordering and shipping details

Category	08469 - SURGE PROTECTION ACCESSORIES
Discount Schedule	DE1B
GTIN	00785901239741
Nbr. of units in pkg.	1
Package weight(Lbs)	0.72 lb(US) (0.33 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	4.50 in (11.430 cm)
Package 1 width	5.40 in (13.716 cm)
Package 1 Length	8.10 in (20.574 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------
