



Main

Circuit breaker type	Standard
Quantity per set	Set of 3
AWG gauge	AWG 14...AWG 2 3 copper
Product destination	HD/HG/HJ/HL circuit breaker 15...100 A

Complementary

Tightening torque	39.83 Lbf.in (4.5 N.m) 0.04...0.08 in ² (25...50 mm ²) (AWG 4...AWG 1) 35.40 Lbf.in (4 N.m) 0.00...0.02 in ² (2.5...16 mm ²) (AWG 14...AWG 6) 39.83 lbf.in (4.5 N.m) 0.02 in ² (10 mm ²)
-------------------	---

Ordering and shipping details

Category	01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	00785901538011
Nbr. of units in pkg.	1
Package weight(Lbs)	0.34 lb(US) (0.15 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.60 in (4.064 cm)
Package 1 width	4.50 in (11.43 cm)
Package 1 Length	5.50 in (13.97 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------