

# SC816D150C

Meter mains, Homeline, combination service entrance, ringed socket, 150A, surface mount, maximum 8 spaces, 16 circuits, no bypass



## Main

Product or component type	Meter Mains
Range of product	Homeline

## Complementary

Line Rated Current	150 A
Short-circuit current	10 kA
Network number of phases	1
Meter socket type	Ringed
Mounting	Surface
Number of spaces	8
Number of circuits	16
Number of Tandem Breakers	8
Hub type	A-L A
Electrical connection	Lugs line side Feed-thru lugs service ground Feed-thru lugs load side
Wire Size	AWG 6...300 kcmil aluminium/copper)line side AWG 12...AWG 1/0 aluminium/copper)service ground AWG 6...250 kcmil aluminium/copper)load side
Tightening torque	Main lugs 250 lb.in, AWG 6...300 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14...AWG 1/0, copper Service ground 50 lb.in, AWG 12...AWG 1/0, aluminium Lugs 250 lb.in, AWG 6...250 kcmil, aluminium/copper Branch lugs 50 lb.in, AWG 3...AWG 1/0, aluminium/copper Branch lugs 45 lb.in, AWG 6...AWG 4, aluminium/copper Branch lugs 40 lb.in, AWG 8, aluminium/copper Branch lugs 35 lb.in, AWG 14...AWG 10, copper Branch lugs 35 lb.in, AWG 12...AWG 10, aluminium Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	150 A
Branch Breaker Rating	100 A
Service feed location	OH UG
Bypass type	No bypass
Height	34.00 in (863.60 mm)
Width	14.95 in (379.73 mm)
Depth	7.12 in (180.85 mm)

## Environment

Product certifications	UL E-6294
------------------------	-----------

## Ordering and shipping details

Category	00048 - HOM METER MAINS
Discount Schedule	DE3A
GTIN	00785901859154
Nbr. of units in pkg.	1
Package weight(Lbs)	52.08 lb(US) (23.62 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	7.50 in (19.050 cm)
Package 1 width	15.60 in (39.624 cm)
Package 1 Length	33.50 in (85.090 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------