



Main

Range of product	Harmony 9001K
Product or component type	Illuminated push-button
Device short name	K
Type of operator	Spring return
Operator profile	Blue projecting
Operator additional information	Without guard

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Light source	incandescent
Bulb base	BA 9s
Light block supply	Via integral transformer
[Us] rated supply voltage	110...120 V AC
Contacts type and composition	1 C/O
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product

Environment

Product certifications	CSA LR 25490 class 3211 03 CE UL listed file E42259 CCN NKCR NEMA
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901027904
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5 lb(US) (0.23 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	5.08 in (12.903 cm)
Package 1 width	2.00 in (5.080 cm)
Package 1 Length	12.90 in (32.774 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------