

USB 3.0 SuperSpeed Extension Cable (AA M/F) Black, 6 ft. (1.83 m)

MODEL NUMBER: U324-006-BK



Extends a USB 3.0 cable an additional 6ft

Features

- 6-ft. USB 3.0 SuperSpeed Extension Cable - Black
- SuperSpeed USB is 10 times faster than Hi-Speed USB, with transfer rates up to 5 Gbps.
- Sync-N-Go technology minimizes user wait-time.
- Provides Optimized Power Efficiency...No device polling and lower active and idle power requirements.
- Backwards compatible with USB 2.0. Devices interoperate with USB 2.0 platforms. Host support USB 2.0 legacy devices.

Specifications

| OVERVIEW | |
|---------------------------|---------------------------|
| UPC Code | 037332183156 |
| Technology | USB 3.0 (SuperSpeed); USB |
| PHYSICAL | |
| Color | Black |
| Cable Outer Diameter (OD) | 5.5MM |
| Cable Jacket Rating | VW-1 |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.8 |
| Material of Construction | PVC |

Highlights

- 6-ft. SuperSpeed USB 3.0 A-A Extension Cable
- 10 times faster than USB 2.0, with transfer rates up to 5 Gbps

System Requirements

- Computers and Peripherals with USB 3.0 capabilities

Package Includes

- 6-ft. SuperSpeed USB 3.0 A-A Extension cable - Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--------------------------------------|--------------------------------|
| Shipping Dimensions (hwd / cm) | 17.78 x 22.86 x 1.27 |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50 |
| Shipping Weight (kg) | 0.08 |
| Shipping Weight (lbs.) | 0.18 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14 to 140 F (-10 to 60 C) |
| Storage Temperature Range | -4 to 185 F (-20 to 85 C) |
| Relative Humidity | 10% to 85%, Non-Condensing |
| CONNECTIONS | |
| Side A - Connector 1 | USB 3.0 A (MALE) |
| Side B - Connector 1 | USB 3.0 A (FEMALE) |
| Connector Plating | Nickel |
| Contact Plating | Gold |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 3.0 (up to 5 Gbps) |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>