

Product data sheet

Characteristics

HOM3060L125PQGC

Load center, Homeline, 1 phase, 30 spaces, 60 circuits, 125A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar



Main

| | |
|--|---|
| Product Type | Load Center |
| Marketing Trade Name | Homeline |
| Load Center Type | Main lugs |
| Rated Current | 125 A |
| Number of Spaces | 30 |
| Maximum Number of Single Pole Circuits | 60 |
| Enclosure Rating | NEMA 1 for indoor |
| Cover Type | Combination flush/surface cover |
| Electrical Connection | Lugs |
| Provided Equipment | Grounding bar 1) Qwik grip assembly kit 1) |

Complementary

| | |
|-----------------------------------|--|
| Max Short Circuit Current Rating | 10 kA |
| Maximum Number of Tandem Breakers | 30 |
| Number of Phases | 1 phase |
| Voltage Rating | 120/240 V AC |
| Wire Size | AWG 6...AWG 2/0 aluminium/copper |
| Ground Bar | Grounding bar included (not installed) |
| Wiring Configuration | 3-wire |
| Enclosure Material | Welded galvanized steel |
| Surface Finish | Baked enamel grey |
| Box Number | 10Q |
| Height | 33.78 in (858 mm) |
| Depth | 3.74 in (95 mm) |
| Width | 14.25 in (362 mm) |

Environment

| | |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature for Operation | 23 °F (-5 °C) 104 °F (40 °C) |
|---------------------------------------|---------------------------------|

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 00045 - HOM LC&CVR,12-42 CKT,NEMA1 |
| Discount Schedule | DE3C |
| GTIN | 00785901776956 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 5.38 in (13.653 cm) |
| Package 1 width | 16.00 in (40.640 cm) |
| Package 1 Length | 36.25 in (92.075 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |