



Main

| | |
|-----------------------------|-------------------------------|
| Product or component type | Miniature circuit-breaker |
| Range of product | QOU |
| Circuit breaker type | Standard |
| Circuit breaker application | HACR and Switching Duty rated |

Complementary

| | |
|--------------------------------|--|
| Line Rated Current | 40 A |
| Electrical connection | Slotted box lugs, line side Slotted box lugs, load side |
| [Ue] rated operational voltage | 120/240 V AC 120 V AC 48 V DC |
| Mounting mode | Unit mount |
| AWG gauge | AWG 14...AWG 2 aluminium/copper |
| Height | 4.05 in (102.87 mm) |
| Width | 1.5 in (38.10 mm) |
| Depth | 2.95 in (74.93 mm) |
| Tightening torque | 45 lbf.in (5.08 N.m) (AWG 14...AWG 2) |

Environment

| | |
|------------------------|-------------------------|
| Product certifications | IEC UL Listed CSA |
|------------------------|-------------------------|

Ordering and shipping details

| | |
|---------------------|-----------------------------|
| Category | 00900-QOU BREAKERS & SWITCH |
| Discount Schedule | DE2 |
| GTIN | 00785901079347 |
| Package weight(Lbs) | 12.96 oz (367.410 g) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 2.20 in (5.588 cm) |
| Package 1 width | 3.70 in (9.398 cm) |
| Package 1 Length | 4.90 in (12.446 cm) |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|