



## Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Number of Poles	3
Current Rating	200 A
Voltage Rating	480 V AC 250 V DC
Enclosure Rating	NEMA 4/4X/5 stainless steel 304
Maximum Horse Power Rating	15 hp 480 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52

## Complementary

Short-circuit current	10 kA H or J
Fuse type	H or J
Mounting Type	Surface
Wire Size	AWG 6...300 kcmil copper or aluminium
Tightening torque	340 lbf.in (38.41 N.m) (AWG 6...300 kcmil)
Depth	11.75 in (298.45 mm)
Width	23.88 in (606.55 mm)
Height	30.88 in (784.35 mm)
Net Weight	136.69 lb(US) (62 kg)

## Ordering and shipping details

Category	00066 - MISC H/D SWITCHES
Discount Schedule	DE1
GTIN	00785901017615
Nbr. of units in pkg.	1
Package weight(Lbs)	126 lb(US) (57.15 kg)
Returnability	Yes
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

---

Warranty

18 months

---