

Main

Device short name	F
Enclosure type	Standard environment enclosure indoor
Factory modification	Low pressure cut-off (AUTO-START-OFF) operates roughly 10 PSIG below cut-in
Product specific application	Control electrically driven water pumps
Quantity per set	Set of 20
Range of product	Square D Pumptrol
Switch application	Standard
Type of packing	Bulk

Complementary

Adjustable range on rising pressure	20...65 psi (137.90...448.16 kPa)
Approximate adjustable differential	15...30 psi (103.42...206.84 kPa)
Depth	2.78 in (70.61 mm)
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.25 inch NPSF internal
Height	2.8 in (71.12 mm)
Material	Zinc plated steel flange
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	220 psig
Maximum Horse Power Rating	2 Hp 115 V AC, 3 phase 1.5 Hp 115 V AC, 1 phase 3 Hp 230 V AC, 3 phase 2 Hp 230 V AC, 1 phase 1 hp 460/575 V AC, 3 phase
Number of poles	2
Permissible voltage	575 V AC
Pressure actuator	Diaphragm
Pressure setting range	30...50 psi (206.84...344.74 kPa)
Net Weight	1.13 lb(US) (0.51 kg)
Range on decreasing pressure	10...45 psi (68.95...310.26 kPa)
Scale type	Adjustable differential
Switch function	DPST
Width	3.76 in (95.50 mm)

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA file LR25490

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21532 - 9013 FSG,FYG (BULK - DISCOUNT CP7)
Discount Schedule	CP7
GTIN	00785901209522
Nbr. of units in pkg.	20
Package weight(Lbs)	0.83 lb(US) (0.38 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.16 in (25.806 cm)
Package 1 width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	17.00 lb(US) (7.711 kg)
Package 2 Height	9.10 in (23.114 cm)
Package 2 width	8.60 in (21.844 cm)
Package 2 Length	18.40 in (46.736 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	400
Package 3 Weight	340.00 lb(US) (154.221 kg)
Package 3 Height	40.00 in (101.6 cm)
Package 3 width	36.00 in (91.44 cm)
Package 3 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------