



Main

Range of product	Powerpact
Product or component type	Power distribution connector
Circuit breaker type	LL LD LJ LG
Quantity per set	Set of 3

Complementary

Line Rated Current	150...600 A
Tightening torque	49.56 Lbf.In (5.6 N.m) 35.40 Lbf.In (4 N.m) 0.00...0.02 in ² (2.5...16 mm ²) 327.48 Lbf.In (37 N.m) 0.04...0.08 in ² (25...50 mm ²) (AWG 8...AWG 6) 20.36 lbf.in (2.3 N.m) 0.00...0.01 in ² (2.5...6 mm ²) (AWG 14...AWG 10)

Environment

Product certifications	UL CSA
------------------------	-----------

Ordering and shipping details

Category	01103-H,J,COMPACT NS UL/IEC CB ACCESS
Discount Schedule	DE2
GTIN	00785901730590
Package weight(Lbs)	16.00 oz (453.592 g)
Returnability	Yes
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.