

Product data sheet

Characteristics

9421V1A30

Manual Motor Switch, TeSys Vario, rotary handle, 20A, 3 pole, 10HP at 480V, metallic enclosure, UL Type 12



Main

Color	Red/yellow
Enclosure type	Dust and damp proof enclosure indoor
Lock type	Padlockable
Range of product	VARIO

Complementary

Line Rated Current	20 A
Auxiliary contact composition	Without
Depth	6.25 in (158.75 mm)
Device mounting	Surface
Enclosure material	Metallic metal
Height	7.38 in (187.45 mm)
Maximum Horse Power Rating	5 Hp 240 V AC 10 hp 480/600 V AC
Permissible voltage	600 V AC
Width	5.5 in (139.70 mm)

Environment

NEMA degree of protection	NEMA 12
Product certifications	UL listed file E164864 CCN NLRV CSA LR81630 class 3211 05

Ordering and shipping details

Category	21730 - V VARIO SWITCH
Discount Schedule	CP1
GTIN	00785901058908
Nbr. of units in pkg.	1
Package weight(Lbs)	3.86 lb(US) (1.751 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.80 in (14.732 cm)
Package 1 width	7.40 in (18.796 cm)
Package 1 Length	7.90 in (20.066 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------