

PC 009



CONTRACTOR GRADE, CO-EXTRUDED DUCT TAPE

TYPICAL APPLICATIONS

- For heavy duty sealing, seaming, repairing, holding and waterproofing applications that require aggressive stick and superior hold
- Also used in the restoration industry for tasks such as holding poly-sheeting
- For temporary or permanent use

PRODUCT FEATURES

- Excellent cold temperature performance
- Aggressive adhesion
- All-weather durability
- Consistent, low-force unwind off the roll
- Hand-tearable in machine and cross directions
- Made using Polybonded CO-EX Technology®

CONSTRUCTION

Overall Grade/Function: Contractor

Backing: Waterproof polyethylene film with a cloth carrier

Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

STANDARD CORE SIZE

3 in

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



SILVER
(SIL)



WHITE
(WHI)



BLACK
(BLK)



RED
(RED)

PHYSICAL PROPERTIES

STANDARD

METRIC

Tensile Strength	26 lbs/in width	45.5 N/10 mm
Adhesion to Stainless Steel	80 oz/in width	8.76 N/10 mm
Thickness	9 mils	0.23 mm
Elongation	20%	20%
Service Temperature Range	35 F to 200 F	2 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PTSC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent product specifications or a guarantee of product performance. Individual rolls may vary from these standards (or physical properties). The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

