

Product data sheet

Characteristics

QON342L225I

Load center accessory, QO, mounting base, 3 phase, 42 spaces, 225A main lugs, OEM, neutral busbar



Main

Product Type	Mounting base
Marketing Trade Name	QO
Voltage Rating	208Y/120 V AC 240 V AC

Complementary

Wire Size	AWG 4...300 kcmil aluminium/copper
Product Certifications	UR
Height	5.99 in (152.15 mm)
Width	10.62 in (269.75 mm)

Ordering and shipping details

Category	00909-MOUNTING BASES, S/N
Discount Schedule	DE3A
GTIN	00785901435549
Package weight(Lbs)	4.98 lb(US) (2.259 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	2.30 in (5.842 cm)
Package 1 width	10.80 in (27.432 cm)
Package 1 Length	32.00 in (81.280 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty

18 months
