



Main

| | |
|-----------------------------|---|
| Range of product | Altivar |
| Product or component type | Digital encoder interface module |
| Range compatibility | Altivar Process ATV900 Altivar Process Modular Altivar Machine ATV340 |
| Communication port protocol | RS422 |
| Encoder type | EnDat 2.2 A/B/I incremental XCC1 type R A/B/I incremental XCC1 type X SSI absolute encoder XCC2 type SG SSI absolute encoder XCC3 type SB |
| [Us] rated supply voltage | 5 V DC 4.75...5.25 V) 12 V DC 11.4...12.6 V) 24 V DC 22.8...25.2 V) |

Complementary

| | |
|--|---|
| Maximum supply current | 0.25 A 5 V DC 0.1 A 12 V DC 0.05 A 24 V DC |
| Protection type | Short-circuit protection Overload protection |
| Maximum cable distance between devices | 328.08 Ft (100 m) A/B/I) 164.04 Ft (50 m) SSI) 328.08 Ft (100 m) SSI)at 300 kHz 164.04 Ft (50 m) EnDat 2.2) 328.08 ft (100 m) EnDat 2.2)with propagation delay compensation |
| Maximum operating frequency | 1000 kHz |
| Input signal | Data+, Data- EnDat 2.2) Data+, Data- SSI) Temp+, Temp- A+,A-/B+,B-/I+,I- A/B/I) TTL |
| Input impedance | 121 Ohm |
| Output signal | Clock+, Clock- SSI) Data+, Data-, Clock+, Clock- EnDat 2.2) |
| Connector type | 1 female high density SUB-D 15 |
| Net Weight | 0.33 lb(US) (0.15 kg) |

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 22209 - ATV650 |
| Discount Schedule | CP4E |
| GTIN | 00785901094005 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.33 lb(US) (0.15 kg) |
| Returnability | Yes |
| Country of origin | ID |

Packing Units

| | |
|------------------|----------|
| Package 1 Height | 0.700 dm |
| Package 1 width | 1.300 dm |
| Package 1 Length | 1.900 dm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |