

Barrel Vacuum

by **Atrix**[™]



High Capacity



ATI55H-3

PRODUCT HIGHLIGHTS

WARRANTY

1 Year Limited

3 MOTOR CONFIGURED VACUUM HEAD

Converts your 55 gallon barrel/drum into a large capacity vacuum

POWERFUL

TRIPLE 550 Watt Motors allows the user to control the amount of suction needed per a wide variety of applications by switching on 1, 2 or all 3 motors

SAFE

Can be used in general cleaning with its efficient two stage HEPA filter configuration

APPLICATIONS

Manufacturing, Construction or other situations where large amounts of non-hazardous dry particulate needs to be collected



Ultrafine Vacuums Built to Last. Quality Assured.

www.atrinx.com | sales@atrinx.com | 1-800-222-6154 | Burnsville, MN, USA

Barrel Vac

by **Atrix™**

SPECIFICATIONS

ATI55H-3

DIMENSIONS

Length: 26" (660 mm)
Width: 26" (660 mm)
Height: 26" (660 mm)

WEIGHT 26 lbs. (11.8 kg)

HOSE DIAMETER

Inside - 2.00" (50.8 mm)
Outside - 2.33" (59.18 mm)

POWER

120v, 550W x 3

CFM

89, 178 or 267

INCLUDED CONTENTS

Barrel Vac by Atrix

- A - 28' Power Cord
- B - ATIBV55-MH - Triple Motor Head
- C - ATIBV55-DA - Barrel/Drum Adapter
- D - ATIBCVH1 - Premotor HEPA Filter Cartridge, Main
- E - ATIBCVSF - Polyester Pretreated Filter for Main HEPA Filter
- F - ATIBV55-12 - 12' Hose w/Ends
- G - ATIBV55-WS - 3 Piece Chrome Wand Set
- H - ATIBV55-FT - Floor Tool



FILTRATION

2 Stage

HEPA Premotor Filter
Polyester Pretreated Filter

GENERAL INFORMATION

PACKAGING

Dimensions: L W H
Inches: 34 26 38
mm: 864 660 965
Weight: 94 lbs.
42.6 kg

HS Code

8508.11.0000

UPC

8 38067 00343 2

OPTIONAL ACCESSORIES

25' Hose w/Ends
ATIBV55-25



Barrel/Drum Roller Base
ATIBV55-RB



55 Gallon Barrel/Drum
ATIBV55-DRUM

