


# Highpointe LED CF205L



- A. Total Fan Height: **16.5/22.5"**
- B. Bottom of Blade to Ceiling: **15/21"**
- C. Width of Canopy: **6.30"**
- D. Width of Housing: **8"**
- E. Total Fan Diameter: **54"**

## LIGHTING

|                |               |
|----------------|---------------|
| AMPS           | <b>0.57</b>   |
| Lumens         | <b>1500</b>   |
| Watts          | <b>18</b>     |
| CRI            | <b>90</b>     |
| CCT (K)        | <b>3000</b>   |
| Dimming Light  | <b>Y</b>      |
| Reverse Switch | <b>Manual</b> |

## PERFORMANCE

| Speed              | High        | Low         |                             |
|--------------------|-------------|-------------|-----------------------------|
| Airflow            | <b>5023</b> | <b>1256</b> | CUBIC FT. PER MIN.          |
| Electricity Use    | <b>67</b>   | <b>7.2</b>  | WATTS (EXCL. LIGHTS)        |
| Airflow Efficiency | <b>75</b>   | <b>173</b>  | CUBIC FT. PER MIN. PER WATT |
| RPM                | <b>165</b>  | <b>45</b>   | REVOLUTIONS PER MIN.        |

## CONTROLS

### Included

**SR400**  
4-Speed  
Remote Control  
with Receiver



### Optional

**SW406**  
4-Speed  
Wall Control



## AVAILABLE FINISHES

### OIL RUBBED BRONZE

**CF205LORB** - Reversible Farmhouse/Coffee Blades, Opal Matte Glass Shade

### GOLDEN ESPRESSO

**CF205LGES** - Chocolate Blades, Sandstone Glass Shade

### NEW! VINTAGE STEEL

**CF205LCVS** - Aged Cedar, Opal Matte Glass Shade

### VINTAGE STEEL

**CF205LVS** - Reversible Riverwash/Honey Oak Blades, Sandstone Glass Shade

### GRAPHITE

**CF205LGRT** - Reversible Timber Gray/Charcoal Blades, Opal Matte Glass Shade

### NEW! BARBEQUE BLACK

**CF205LBQ** - Reversible Charcoal/Black Blades, Opal Matte Glass Shade

## ENERGYGUIDE

Estimated  
Yearly Energy Cost

# \$11

Cost Range of Similar Models (19" - 84")  
\$3 | | | \$34

• Based on 12 cents per kWh and 6.4 hours use per day  
• Your cost depends on rates and use  
• Energy Use: 41 Watts

Airflow

# 3,257

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
• Airflow Efficiency: 80 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

Energy information listed above is a weighted average of High and Low speeds tested with the downrod supplied.



A Division of Luminance Brands

1945 S. Tubeway Ave.  
Los Angeles, CA 90040

## CUSTOMER SERVICE

Tel: 800.346.1340  
Fax: 800.346.1381  
Email: [Sales@LuminanceBrands.com](mailto:Sales@LuminanceBrands.com)

For our full line of products, visit [LuminanceBrands.com](http://LuminanceBrands.com)



## FAN SPECIFICATIONS

|                      |                     |
|----------------------|---------------------|
| Diameter             | <b>54"</b>          |
| Motor Lead Lengths   | <b>80"</b>          |
| Motor Size (mm)      | <b>155 x 22</b>     |
| Product Weight       | <b>22.30</b> LBS    |
| Blade Pitch          | <b>14°</b>          |
| Downrod Length       | <b>6"/12" INCL.</b> |
| Accepts 2.5" Downrod | <b>Y</b>            |

## SHIPPING SPECIFICATIONS

|               |               |
|---------------|---------------|
| Carton Weight | <b>27</b> LBS |
| Length        | <b>25.1"</b>  |
| Width         | <b>15.2"</b>  |
| Depth         | <b>12.2"</b>  |