


Keane CF320



- A. Total Fan Height: **10.9"**
- B. Bottom of Blade to Ceiling: **10.4"**
- C. Width of Canopy: **5.9"**
- D. Width of Housing: **11"**
- E. Total Fan Diameter: **52"**

LIGHTING

AMPS	0.45
Lumens	N/A
Watts	N/A
CRI	N/A
CCT (K)	N/A
Dimming Light	N/A
Reverse Switch	Manual

PERFORMANCE

Speed	High	Low	
Airflow	4357	1885	CUBIC FT. PER MIN.
Electricity Use	54	12.3	WATTS (EXCL. LIGHTS)
Airflow Efficiency	81	153	CUBIC FT. PER MIN. PER WATT
RPM	175	75	REVOLUTIONS PER MIN.

CONTROLS

Included

SW46W
4-Speed
Slide Control




CF320 X XX

Keane model # **1** **2**

1. Choose blades



2. Choose fan finish



ENERGYGUIDE

<p>Estimated Yearly Energy Cost</p> <h1 style="font-size: 2em;">\$10</h1> <p>Cost Range of Similar Models (19" - 84") \$3 \$34</p> <p><small>* Based on 12 cents per kWh and 6.4 hours use per day * Your cost depends on rates and use * Energy Use: 34 Watts</small></p>	<p>Airflow</p> <h1 style="font-size: 2em;">3,198</h1> <p>Cubic Feet Per Minute</p> <p><small>* The higher the airflow, the more air the fan will move * Airflow Efficiency: 93 Cubic Feet Per Minute Per Watt</small></p>
--	---

All estimates based on typical use, excluding lights ftc.gov/energy

Energy information listed above is a weighted average of High and Low speeds tested with the downrod supplied.

AVAILABLE FINISHES

- | | |
|---|--|
| <p>BRUSHED STEEL
CF320SBS - Brushed Steel/Barbeque Black Blades</p> <p>BRUSHED STEEL
CF320CBS - Natural Cherry/Walnut Blades</p> <p>BRUSHED STEEL
CF320RBS - Charcoal/Timber Gray Blades</p> <p>SATIN WHITE
CF320WSW - Satin White/Maple Blades</p> <p>GRAPHITE
CF320RGRT - Charcoal/Timber Gray Blades</p> <p>SATIN WHITE
CF320RSW - Charcoal/Timber Gray Blades</p> | <p>BRUSHED STEEL
CF320WBS - Satin White/Maple Blades</p> <p>SATIN WHITE
CF320CSW - Natural Cherry/Walnut Blade</p> <p>SATIN WHITE
CF320SSW - Brushed Steel/Barbeque Black Blades</p> <p>GRAPHITE
CF320CGRT - Natural Cherry/Walnut Blades</p> <p>GRAPHITE
CF320WGRT - Satin White/Maple Blades</p> <p>GRAPHITE
CF320SGRT - Brushed Steel/Barbeque Black Blades</p> |
|---|--|

CONTINUE ▶



A Division of Luminance Brands

1945 S. Tubeway Ave.
Los Angeles, CA 90040

CUSTOMER SERVICE

Tel: 800.346.1340
Fax: 800.346.1381
Email: Sales@LuminanceBrands.com

For our full line of products, visit LuminanceBrands.com



FAN SPECIFICATIONS

Diameter	52"
Motor Lead Lengths	80"
Motor Size (mm)	153 x 17
Product Weight	18 LBS
Blade Pitch	12°
Downrod Length	4.5" INCL.
Accepts 2.5" Downrod	N

SHIPPING SPECIFICATIONS

Carton Weight	22 LBS
Length	27"
Width	12"
Depth	11"