


Aira Eco LED CF985L



- A. Total Fan Height: **14.40"**
- B. Bottom of Blade to Ceiling: **12.50"**
- C. Width of Canopy: **6.40"**
- D. Width of Housing: **8.40"**
- E. Total Fan Diameter: **72"**

LIGHTING

AMPS	0.52
Lumens	1500
Watts	18
CRI	90
CCT (K)	3000
Dimming Light	Y
Reverse Switch	Remote

PERFORMANCE

Speed	High	Low	
Airflow	8133	3018	CUBIC FT. PER MIN.
Electricity Use	32	4	WATTS (EXCL. LIGHTS)
Airflow Efficiency	254	834	CUBIC FT. PER MIN. PER WATT
RPM	90	30	REVOLUTIONS PER MIN.

CONTROLS

Included

6-Speed Wall Control with Receiver



Optional

SR600
6-Speed Remote Control



SR650²
6-Speed 2-in-1 Remote Control



¹ Damp Location rated for ORB, GRT and PT finish. BS finish not suitable for damp locations.

² Controls are recommended for indoor use only.

AVAILABLE FINISHES

GRAPHITE CF985LGRT - Weather-Resistant Driftwood Blades, Opal Matte Glass Shade

OIL RUBBED BRONZE CF985LORB - Weather-Resistant Walnut Blades, Opal Matte Glass Shade

BRUSHED STEEL¹ CF985LBS - Walnut Blades, Opal Matte Glass Shade

PLATINUM CF985LPT - Weather-Resistant Platinum Blades, Opal Matte Glass Shade

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$6

Cost Range of Similar Models (19" - 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 21 Watts

Airflow

5,735

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 270 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

Energy information listed above is a weighted average of High and Low speeds tested with the downrod supplied.



A Division of Luminance Brands

1945 S. Tubeway Ave.
Los Angeles, CA 90040

CUSTOMER SERVICE

Tel: 800.346.1340
Fax: 800.346.1381
Email: Sales@LuminanceBrands.com

For our full line of products, visit LuminanceBrands.com



PREMIUM DC
ECOMOTOR



DAMP
LOCATION



INTEGRATED
LED LIGHTING



SHIPS TO
CANADA



LIMITED
LIFETIME
MOTOR
WARRANTY

FAN SPECIFICATIONS

Diameter	72"
Motor Lead Lengths	80"
Motor Size (mm)	165 DC
Product Weight	32 LBS
Blade Pitch	15°
Downrod Length	6" INCL.
Accepts 2.5" Downrod	Y

SHIPPING SPECIFICATIONS

Carton Weight	36 LBS
Length	32.3"
Width	10.3"
Depth	11.3"