

CRYSTAL LIGHT ON THE GO POWDERED SOFT DRINK ICED TEA SUGAR FREE

Dot #:

449882

Mfr #:

10043000007577

GTIN:

10043000007577

Supplier:

Kraft US (0044710044602)

Description:

CRYSTAL LIGHT ON THE GO POWDERED SOFT DRINK ICED TEA SUGAR FREE

Images and Attachments



Product Information

Classification:

Drinks Flavoured - Not Ready to Drink (10000202)

Dimensions (HxWxD):

6.12 x 6 x 8.75 Inch

Weight Gross / Net:

1.55 Pound / 0.6 Pound

Origin:

(US) UNITED STATES

Storage Temperature:

-50° to 150°

Pallet Configuration:

Ti: Hi:

Servings Per Container:

75

Features and Benefits (Case GTIN: 1004300007577)Feares:

Sugar-free with just 5 calories per serving/ Instant Dissolve technology allows for quick preparation and consistent quality of finished product/ On the go packets make Crystal Light easy to take with you //

Preparation and Cooking:

Reconstitute - Tear open stick packet, pour into 20 oz. water (bottle or cup), shake or stir to mix. Can be mixed in 16.9 oz. of water for a slightly stronger flavor.

Serving Suggestions:

blank

Storage:

BOX/CARTON Corrugated or Solid Ambient Prevailing Conditions

Features and Benefits (Inner GTIN: 00043000840771)

Storage:

BOX/CARTON Fiber Ambient Prevailing Conditions

Features and Benefits (Consumer or Base GTIN: 0004300007570)

Storage:

WRAPPER Plastic Ambient Prevailing Conditions

Nutritionals and Ingredients (Case GTIN: 1004300007577)

Representation of label(s). The actual nutritional label(s) on the package may vary slightly

Nutrition Facts (Unprepared)	
Serving Size	1 g
Servings Per Container	75
Amount Per Serving	
Calories	5.0
Calories from fat	0.0
% Daily Value*	
Saturated Fat	0.0 g 0.0%
Trans Fat	0.0 g
Cholesterol	0.0 mg 0.0%
Sodium	0.0 mg 0.0%
Potassium	10.0 mg 0.0%
Total Carbohydrate	0.0 g 0.0%
Dietary Fiber	0.0 g 0.0%
Sugar	0.0 g
Protein	0.0 g

Calcium		0.0%
Iron		0.0%
Phosphorous		0.0%
(-) Information is currently not available for this nutrient.		
* Percent Daily Values are based on a 2,000 calorie diet. Your daily values may be higher or lower depending on your calorie needs:**		
** Percent Daily Values listed below are intended for adults and children over 4 years of age. Foods represented or purported to be for use by infants, children less than 4 years of age, pregnant women, or lactating women shall use the RDI's that are specified for the intended group provided by the FDA.		
	Calories:	2,000 2,500
Total Fat	Less than	65g 80g
Sat. Fat	Less than	20g 25g
Cholesterol	Less than	300mg 300mg
Sodium	Less than	2400mg 2400mg
Potassium		3500mg 3500mg
Total Carbohydrates		300mg 3500mg
Dietary Fiber		25mg 30mg
Calories per gram:		
	Fat 9	Carbohydrate 4 Protein 4

Ingredients: INGREDIENTS: CITRIC ACID, MALTODEXTRIN, CORN SYRUP SOLIDS*, INSTANT TEA, ASPARTAME**, CONTAINS LESS THAN 2% OF NATURAL FLAVOR, MAGNESIUM OXIDE, ACESULFAME POTASSIUM, RED 40, YELLOW 5, BLUE 1, BHA (PRESERVES FRESHNESS). * ADDS A TRIVIAL AMOUNT OF SUGAR** PHENYLKETONURICS: CONTAINS PHENYLALANINE

Nutritionals and Ingredients (Inner GTIN: 00043000840771)

Representation of label(s). The actual nutritional label(s) on the package may vary slightly

Nutrition Facts (Unprepared)	
Serving Size	1 g
Servings Per Container	75
Amount Per Serving	
Calories	5.0
	Calories from fat 0.0
	% Daily Value*
Saturated Fat	0.0 g 0.0%
Trans Fat	0.0 g
Cholesterol	0.0 mg 0.0%
Sodium	0.0 mg 0.0%
Potassium	10.0 mg 0.0%
Total Carbohydrate	0.0 g 0.0%

Dietary Fiber	0.0 g	0.0%
Sugar	0.0 g	
Protein	0.0 g	
Calcium		0.0%
Iron		0.0%
Phosphorous		0.0%
(-) Information is currently not available for this nutrient.		
* Percent Daily Values are based on a 2,000 calorie diet. Your daily values may be higher or lower depending on your calorie needs:**		
** Percent Daily Values listed below are intended for adults and children over 4 years of age. Foods represented or purported to be for use by infants, children less than 4 years of age, pregnant women, or lactating women shall use the RDI's that are specified for the intended group provided by the FDA.		
	Calories:	2,000 2,500
Total Fat	Less than	65g 80g
Sat. Fat	Less than	20g 25g
Cholesterol	Less than	300mg 300mg
Sodium	Less than	2400mg 2400mg
Potassium		3500mg 3500mg
Total Carbohydrates		300mg 3500mg
Dietary Fiber		25mg 30mg
Calories per gram:		
	Fat 9	Carbohydrate 4 Protein 4

Ingredients: INGREDIENTS: CITRIC ACID, MALTODEXTRIN, CORN SYRUP SOLIDS*, INSTANT TEA, ASPARTAME**, CONTAINS LESS THAN 2% OF NATURAL FLAVOR, MAGNESIUM OXIDE, ACESULFAME POTASSIUM, RED 40, YELLOW 5, BLUE 1, BHA (PRESERVES FRESHNESS).* ADDS A TRIVIAL AMOUNT OF SUGAR** PHENYLKETONURICS: CONTAINS PHENYLALANINE

Nutritionals and Ingredients (Consumer or Base GTIN: 00043000007570)

Representation of label(s). The actual nutritional label(s) on the package may vary slightly

Nutrition Facts (Unprepared)		
Serving Size	1 g	
Amount Per Serving		
Calories	5.0	Calories from fat 0.0
		% Daily Value*
Saturated Fat	0.0 g	0.0%
Trans Fat	0.0 g	
Cholesterol	0.0 mg	0.0%
Sodium	0.0 mg	0.0%

Potassium	10.0 mg	0.0%
Total Carbohydrate	0.0 g	0.0%
Dietary Fiber	0.0 g	0.0%
Sugar	0.0 g	
Protein	0.0 g	
Calcium		0.0%
Iron		0.0%
Phosphorous		0.0%
(-) Information is currently not available for this nutrient.		
* Percent Daily Values are based on a 2,000 calorie diet. Your daily values may be higher or lower depending on your calorie needs:**		
** Percent Daily Values listed below are intended for adults and children over 4 years of age. Foods represented or purported to be for use by infants, children less than 4 years of age, pregnant women, or lactating women shall use the RDI's that are specified for the intended group provided by the FDA.		
<hr/>		
	Calories:	2,000 2,500
Total Fat	Less than	65g 80g
Sat. Fat	Less than	20g 25g
Cholesterol	Less than	300mg 300mg
Sodium	Less than	2400mg2400mg
Potassium		3500mg3500mg
Total Carbohydrates		300mg 3500mg
Dietary Fiber		25mg 30mg
Calories per gram:		
	Fat 9	Carbohydrate 4 Protein 4

Ingredients: INGREDIENTS: CITRIC ACID, MALTODEXTRIN, CORN SYRUP SOLIDS*, INSTANT TEA, ASPARTAME**, CONTAINS LESS THAN 2% OF NATURAL FLAVOR, MAGNESIUM OXIDE, ACESULFAME POTASSIUM, RED 40, YELLOW 5, BLUE 1, BHA (PRESERVES FRESHNESS).* ADDS A TRIVIAL AMOUNT OF SUGAR** PHENYLKETONURICS: CONTAINS PHENYLALANINE

Allergens and Diet (Case GTIN: 10043000007577)

Allergen Information Not Available

Suitable For Diet

Kosher Yes

Organic Not Organic

Allergens and Diet (Inner GTIN: 00043000840771)

Allergen Information Not Available

Suitable For Diet

Kosher Yes

Allergens and Diet (Consumer or Base GTIN: 00043000007570)

Allergen Information Not Available

Suitable For Diet

Kosher Yes

Organic

Not Organic

Powered by [Sync/PDI](#)

This communication is intended for the use of the addressee only and may contain information that is privileged or confidential. If you are not the addressee, you are hereby notified that any dissemination, distribution or use of this communication is prohibited. If you received this communication in error, please destroy it, all copies and any attachments and notify the sender as soon as possible. Any comments, statements or opinions expressed in this communication do not necessarily reflect those of Kraft Heinz Company, its subsidiaries and affiliates.

Ce message est uniquement destiné au destinataire et pourrait contenir des renseignements privilégiés ou confidentiels. Si vous n'êtes pas le destinataire prévu, sachez que toute diffusion, distribution ou utilisation de ce message est interdite. Si vous avez reçu ce message par erreur, nous vous prions d'en aviser l'expéditeur dès que possible et de détruire le message, ainsi que toute copie ou pièce jointe, le cas échéant. Tout commentaire, énoncé ou opinion exprimés dans ce message ne reflètent pas nécessairement ceux de la Kraft Heinz Company, ni de ses filiales ou sociétés affiliées.

