

KETCHAM TECHNICAL DATA

Deluxe Series

Single Door Medicine Cabinet



Model 192PE

Recessed Data

Stainless Steel Framed	Polished Edge Mirror	Beveled Edge Mirror	Overall Size W x H x D	Wall Opening W x H x D	Glass Shelves
160	160PE	160BV	14" x 20" x 4 1/2"	12" x 18 1/4" x 3 1/8"	2
170	170PE	170BV	12" x 36" x 4 1/2"	10" x 34 1/4" x 3 1/8"	4
171	171PE	171BV	16" x 22" x 4 1/2"	14" x 18 1/4" x 3 1/8"	2
172	172PE	172BV	16" x 22" x 4 1/2"	14" x 20 1/4" x 3 1/8"	2
173	173PE	173BV	16" x 30" x 4 1/2"	14" x 28 1/4" x 3 1/8"	3
174	174PE	174BV	18" x 24" x 4 1/2"	16" x 22 1/4" x 3 1/8"	3
175	175PE	175BV	16" x 26" x 4 1/2"	14" x 24 1/4" x 3 1/8"	3
176	176PE	176BV	20" x 26" x 4 1/2"	18" x 24 1/4" x 3 1/8"	3
177	177PE	177BV	16" x 36" x 4 1/2"	14" x 34 1/4" x 3 1/8"	4
178	178PE	178BV	18" x 36" x 4 1/2"	16" x 34 1/4" x 3 1/8"	4
179	179PE	179BV	18" x 42" x 4 1/2"	16" x 40 1/4" x 3 1/8"	4
180	180PE	180BV	18" x 60" x 4 1/2"	16" x 58 1/4" x 3 1/8"	5
181	181PE	181BV	18" x 30" x 4 1/2"	16" x 28 1/4" x 3 1/8"	3
182	182PE	182BV	20" x 30" x 4 1/2"	18" x 28 1/4" x 3 1/8"	3
184	184PE	184BV	24" x 24" x 4 1/2"	22" x 22 1/4" x 3 1/8"	3
190	190PE	190BV	24" x 30" x 4 1/2"	22" x 28 1/4" x 3 1/8"	4
192	192PE	192BV	24" x 36" x 4 1/2"	22" x 34 1/4" x 3 1/8"	4

Projection is 1 1/2" for the above models

Specifications: White baked enamel steel 20 gauge rust resistant bodies and doors.

Mirrors/Doors: 3/16" first quality plate glass. Doors are mounted on a full length piano hinge and are equipped with a magnetic door catch. Cabinets can be inverted in the field for right or left door swing.

Shelves: 1/4" adjustable tempered glass shelves mounted on locking adjustable aluminum shelf clips.

3505 Veterans Memorial Hwy., Suite S1
Ronkonkoma NY 11779



631-615-6151
www.ketchamcabinets.com