

Flange & Gasket with Urethane



DESCRIPTION

Black Swan's Flange & Gasket with Urethane is a urethane gasket made of a tough, flexible and durable urethane foam. This urethane gasket is then impregnated with wax. The combination of urethane foam and the wax makes for a stronger, more resilient ring than regular rings and is guaranteed for 10 years. Can be used for setting all floor outlet toilet bowls. The gasket forms a water tight, gas tight and odor tight seal. Fits 3" and 4" waste lines. Meets Federal Specification TT-P-1536A.

This ring has a plastic flange which extends the discharge opening. This makes for a more positive seal and assures proper bowl alignment. For certain locations throughout the United States local codes require the plastic flange to fit 4" openings only. Black Swan does have this product available (Stock No. 4570).

DIRECTIONS

1. Be sure the wax ring is at room temperature (about 70° F). If wax ring is too cold a good seal may not be made or the toilet bowl could crack while making the installation.
 2. With the toilet bowl upside down on a protective pad or blanket, place the wax ring around the discharge opening. Press firmly to assure adhesion when the toilet is inverted.
 3. Using the **Black Swan's Stainless or Stay Soft Putty**, make a putty ring about 1 inch high around the outside rim of the toilet. This will make a seal between the toilet rim and the floor.
 4. Carefully set the toilet down on bolts and twist bowl slightly to spread wax and putty to make a tight seal. Tighten bolts carefully to prevent breaking the bowl.
-

ACCESSORIES

Black Swan also sells **Flange & Gasket with Urethane** with closet bolts included in the package. Since closet bolts are necessary to make the installation, this is a nice package to offer the end user.

1. Stock number 04455 is **Flange & Gasket with Urethane** with two 1/4" X 2-1/4" brass bolts, two brass plated nuts, two brass plated washers, and two plastic stand-up washers.

2. Stock number 04456 is **Flange & Gasket with Urethane** with two 1/4" X 2-1/4" brass bolts, four brass plated nuts and four brass plated washers.

3. Stock number 04460 is **Flange & Gasket with Urethane** with two 1/4" X 2-1/4" brass plated bolts, two brass plated nuts, two brass plated washers and two plastic stand-up washers.

4. Stock number 04461 is **Flange & Gasket with Urethane** with two 1/4" X 2-1/4" brass plated bolts, four brass plated nuts and four brass plated washers.

GHS LABEL INFORMATION

PICTOGRAM: None

SIGNAL WORD: None

HAZARDOUS STATEMENT: None

PRECAUTIONARY STATEMENTS

FIRST AID:

Skin: First aid is not normally required. Wash affected area thoroughly with waterless cleaner and/or soap and water. If irritation persists, consult a physician.

Eyes: First aid is not normally required. Flush with large amounts of water for 15 minutes, holding eyelids open. Consult a physician if irritation persists.

Ingestion: First aid is not normally required. If swallowed, give two glasses of water to drink. Never give anything by mouth to an unconscious person. Do not induce vomiting. Consult a physician.

Inhalation: None

STORAGE:

Store away from flame, heat (110° F maximum to keep wax rings from melting or deforming in shape) and strong oxidizing agents. Do not stack cases more than seven high on each pallet. .

DISPOSAL:

Dispose of container in accordance with federal, state or local regulations.

UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
04450	---	0 54647 04450 7	1.37
04455	---	0 54647 04455 2	1.37
04456	---	0 54647 04456 9	1.37
04460	---	0 54647 04460 6	1.37
04461	---	0 54647 04461 3	1.37