

# CP 66L



## CONTRACTOR GRADE, HIGH ADHESION MASKING TAPE

### TYPICAL APPLICATIONS

- For residential and commercial painting and construction, industrial masking, holding and packaging
- Use in applications that demand quick stick and conformability to irregularly shaped surfaces

### PRODUCT FEATURES

- High adhesion
- Easy to unwind
- Good quick stick
- Conforms well to irregularly shaped surfaces
- 3-day clean removal

### CONSTRUCTION

Overall Grade/Function: Contractor  
Backing: Crepe paper  
Adhesive: Rubber-based

### STANDARD WIDTH(S)

12 mm 18 mm 24 mm 36 mm 48 mm 72 mm

### STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

### APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



### PHYSICAL PROPERTIES

|                             | STANDARD        | METRIC       |
|-----------------------------|-----------------|--------------|
| Tensile Strength            | 23 lbs/in width | 40.3 N/10 mm |
| Adhesion to Stainless Steel | 38 oz/in width  | 4.16 N/10 mm |
| Thickness                   | 5.4 mils        | 0.14 mm      |
| Elongation                  | 10%             | 10%          |
| Service Temperature Range   | 50 F to 150 F   | 10 C to 66 C |

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

