

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400083-020

Fontayne

With updated designs that honor the charm of early American styling, Fontayne twelve-light chandelier provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations of Antique Bronze with faux oak accents.

- Features updated designs that honor the charm of early American styling
- Dramatic circular frame offers a stylish perch for graceful candelabra lights
- Dual tone finish combination is Antique Bronze with hand painted weathered oak accents
- Two-tier chandelier uses twelve 60 watt max. candelabra base lamps
- Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces
- Ideal for welcoming guests and visitors in a foyer or entryway, as well as in dining room or traditional living room settings
- Progress Lighting Design Series, a collection offering fashionable styles and affordable luxury.

Category: Chandeliers

Finish: Antique Bronze (painted)

Construction: Steel Construction



Diameter: 32"

Height: 28-3/4"

Overall Ht. W/Chain: 107"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Hanging mounted Mounting strap for outlet box included Ten feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 0.75" ht., 5.125" depth	15 feet of wire supplied 120 V	Quantity: Twelve 60w max. Candelabra Base E12 base	cETLus Dry location listed 1 year limited warranty