


DC POWER SUPPLY: 24 VAC TO 1.5 - 28 VDC

PSMN24DAS

2.75" Track Mount **Non-Isolated** Linear DC Power Supply, 24Vac to 1.5-28 Vdc, 300 mA Adjustable Output, **with Switch**



SPECIFICATIONS

Voltage Input: 24 Vac, full-wave rectified
Voltage Output: 1.5 - 28 Vdc **non-isolated**
Frequency: 50/60 Hz
Overload Protection: Electrical and Thermal, Auto-Reset
Operating Temperature: -30 to 140° F
Humidity Range: 5 to 95% (noncondensing)
Power Status: LED On = Activated
Dimensions: 1.500" x 2.750" x 1.750"
Track Mount: 2.750"
 MT212-2 Mounting Track Supplied
 2 Position Toggle (PSMN24DAS)
Approvals: Class 2 (UL Approved UL5085-3), UL916, C-UL, CE, RoHS

Output Current Ratings:
 116 mA @ 10 Vdc
 125 mA @ 12 Vdc
 300 mA @ 24 Vdc

Input Current Rating:
 550 mA Maximum

Percent Ripple:
 0.0016%, 24 Vdc @ 300 mA

Regulation:
 Load: 0.04% No Load to Full Load
 Line: 0.0125 V/V

Notes:
 • Requires a separate ungrounded transformer when used in conjunction with 1/2 wave rectified power supplies, grounded 24 Vac transformers, or when 24 Vac and 24 Vdc are connected in common.