

# Swan Wax with Urethane



## DESCRIPTION

**Black Swan's Swan Wax with Urethane** is a urethane gasket made of a tough, flexible and durable urethane foam. This urethane gasket is then impregnated with wax. The combination of the urethane foam and the wax makes for a stronger, more resilient ring than regular rings and is guaranteed for 10 years. Can be used for setting all floor outlet toilet bowls. The gasket forms a water tight, gas tight and odor tight seal. Fits 3" and 4" waste lines. Meets Federal Specification TT-P-1536A.

---

## DIRECTIONS

1. Be sure the wax ring is at room temperature (about 70° F). If wax ring is too cold a good seal may not be made or the toilet bowl could crack while making the installation.
  2. With the toilet bowl upside down on a protective pad or blanket, place the wax ring around the discharge opening. Press firmly to assure adhesion when the toilet is inverted.
  3. Using the **Black Swan's Stainless** or **Stay Soft Putty**, make a putty ring about 1 inch high around the outside rim of the toilet. This will make a seal between the toilet rim and the floor.
  4. Carefully set the toilet down on bolts and twist bowl slightly to spread wax and putty to make a tight seal. Tighten bolts carefully to prevent breaking the bowl.
- 

## ACCESSORIES

**Black Swan** also sells **Swan Wax with Urethane** with closet bolts included in the package. Since closet bolts are necessary to make the installation, this is a nice package to offer the end user.

1. Stock number 04335 is **Swan Wax with Urethane** with two 1/4" X 2-1/4" brass bolts, two brass plated nuts, two brass plated washers, and two plastic stand-up washers.
  2. Stock number 04336 is **Swan Wax with Urethane** with two 1/4" X 2-1/4" brass bolts, four brass plated nuts and four brass plated washers.
  3. Stock number 04340 is **Swan Wax with Urethane** with two 1/4" X 2-1/4" brass plated bolts, two brass plated nuts, two brass plated washers and two plastic stand-up washers.
  4. Stock number 04341 is **Swan Wax with Urethane** with two 1/4" X 2-1/4" brass plated bolts, four brass plated nuts and four brass plated washers.
- 

## GHS LABEL INFORMATION

**PICTOGRAM:** None

**SIGNAL WORD:** None

**HAZARDOUS STATEMENT:** None

### PRECAUTIONARY STATEMENTS

#### FIRST AID:

**Skin:** First aid is not normally required. Wash affected area thoroughly with waterless cleaner and/or soap and water. If irritation persists, consult a physician.

**Eyes:** First aid is not normally required. Flush with large amounts of water for 15 minutes, holding eyelids open. Consult a physician if irritation persists.

**Ingestion:** First aid is not normally required. If swallowed, give two glasses of water to drink. Never give anything by mouth to an unconscious person. Do not induce vomiting. Consult a physician.

**Inhalation:** None

#### STORAGE:

Store away from flame, heat (110° F maximum to keep wax rings from melting or deforming in shape) and strong oxidizing agents. Do not stack cases more than seven high on each pallet. .

#### DISPOSAL:

Dispose of container in accordance with federal, state or local regulations.

---

### UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
04330	---	0 54647 04330 2	1.37
04335	---	0 54647 04335 7	1.37
04336	---	0 54647 04336 4	1.37
04340	---	0 54647 04340 1	1.37
04341	---	0 54647 04341 8	1.37