



Model R-3630PE

Fully Recessed Data

Fully recessed cabinets have a 3/4" projection from face of mirror to the wall

Stainless Steel Trim	Polished Edge Mirror	Beveled Edge Mirror	Overall Size W x H x D	Fixed Metal Shelves	Wall Opening W x H x D
R-2430	R-2430PE	R-2430BV	24" x 30" x 4"	3	22" x 28 1/4" x 3-1/8"
R-3030	R-3030PE	R-3030BV	30" x 30" x 4"	3	28" x 28 1/4" x 3-1/8"
R-3036	R-3036PE	R-3036BV	30" x 36" x 4"	3	28" x 34 1/4" x 3-1/8"
R-3630	R-3630PE	R-3630BV	36" x 30" x 4"	4	34" x 28 1/4" x 3-1/8"
R-3636	R-3636PE	R-3636BV	36" x 36" x 4"	4	34" x 34 1/4" x 3-1/8"
R-4830	R-4830PE	R-4830BV	48" x 30" x 4"	3	46" x 28 1/4" x 3-1/8"
R-4836	R-4836PE	R-4836BV	48" x 36" x 4"	4	46" x 34 1/4" x 3-1/8"
R-6036	R-6036PE	R-6036BV	60" x 36" x 4"	4	58" x 34 1/4" x 3-1/8"

Features: Pan door construction for inset European hinge design. Door operates without the use of magnetic closure, this hinging arrangement allows for six way door adjustment. The cabinets are equipped with rubber door silencer pads. Fixed metal shelves are provided with the same gauge and finish as the cabinet body.

Specifications: Tri-View Cabinets are fabricated with 20 gauge white baked enamel steel bodies, doors and shelves.

Mirror/Door: 3/16" first quality plate glass. Pan doors are equipped with cabinet style hinges to allow six way adjustment. Door thickness is 3/4" on all models.

Special sizes are available upon request for large quantities.