



Model SM-2430PE

Surface Mounted Data

Surface Mounted cabinets are 5 1/4" deep from face of mirror to the wall

Stainless Steel Trim	Polished Edge Mirror	Beveled Edge Mirror	Overall Size W x H x D	Fixed Metal Shelves
N/A	N/A	SM-2424BV	24" x 24" x 5 1/4"	3
SM-2430	SM-2430PE	SM-2430BV	24" x 30" x 4-3/4"	3
SM-3030	SM-3030PE	SM-3030BV	30" x 30" x 4-3/4"	3
SM-3036	SM-3036PE	SM-3036BV	30" x 36" x 4-3/4"	3
SM-3630	SM-3630PE	SM-3630BV	36" x 30" x 4-3/4"	4
SM-3636	SM-3636PE	SM-3636BV	36" x 36" x 4-3/4"	4
SM-4830	SM-4830PE	SM-4830BV	48" x 30" x 4-3/4"	3
SM-4836	SM-4836PE	SM-4836BV	48" x 36" x 4-3/4"	4
SM-6036	SM-6036PE	SM-6036BV	60" x 36" x 4-3/4"	4

Features: Pan door construction for inset European hinge design. Door operates without the use of magnetic closure, this hinging arrangement allows for six way door adjustment. The cabinets are equipped with rubber door silencer pads. Fixed metal shelves are provided with the same gauge and finish as the cabinet body.

Specifications: Tri-View Cabinets are fabricated with 20 gauge white baked enamel steel bodies, doors and shelves.

Mirror/Door: 3/16" first quality plate glass. Pan doors are equipped with cabinet style hinges to allow six way adjustment. Door thickness is 3/4" on all models.