

# Product Compatibility Guide

 EnviroAlert  
 Professional®


## EnviroAlert®



Description/Model Name	EA Pro-GTWY	EA Pro-WMFT	EA200-12	EA200-24	EA400-12	EA400-24
Stainless Steel Temp Sensor (Red) TEMP-H-S Range: 32 to 302 °F (0 to 150 °C)	✓	✓	✓	✓	✓	✓
Stainless Steel Temp Sensor (Blue) TEMP-L-S Range: -58 to +158 °F (-50 to +70 °C)	✓	✓	✓	✓	✓	✓
Waterproof High Temp Sensor (Red) TEMP-H-W Range: 32 to 221 °F (0 to 105 °C)	✓	✓	✓	✓	✓	✓
Waterproof Low Temp Sensor (Blue) TEMP-L-W Range: -58 to +158 °F (-50 to +70 °C)	✓	✓	✓	✓	✓	✓
Ultra Low Temp Sensor (White) TEMP-UL-S Range: -148 to +32 °F (-100 to 0 °C)	✓	✓				
EAPro Ultra Low Temp Sensor (RTD-PT 1000) EAPro-ULS Range: -148 to +257 °F (-100 to +125 °C)	✓	✓				
Temperature Probe Housing TEMP-P-H (for use with TEMP-H-W & TEMP-L-W)	✓	✓	✓	✓	✓	✓
Bottle of Glycerin TEMP-G-B	✓	✓	✓	✓	✓	✓
Temp Probe Buffer Kit TEMP-B-T	✓	✓	✓	✓	✓	✓
Temp Probe Flat Cable Splice Kit TEMP-S-K	✓	✓	✓	✓	✓	✓
EAPro Wireless Humidity Sensor EAPro-WHS Range: 5 to 95% RH	✓					
EAPro Wireless Temp Sensor EAPro-WTS Range: 32 to 122 °F (0 to 50°C)	✓					
Wireless Multi-Function Transmitter EAPro-WMFT (HA-III+ or H-4 do not work with the EAPro-WMFT)	✓					
Humidity Sensor HA-4 Range: 5 to 95% RH with ±3% from 25 to 75% RH at 77 °F (25 °C)	✓		✓	✓	✓	✓
Supervised Water Sensor W-S-S	✓	✓	✓	✓	✓	✓
12V DC Power Adapter Kit 110V AC ~ 240V AC to 12V DC @ 1A max Power Adapter Kit 12VDC-KIT (Medical rated)	✓	✓	✓		✓	
12V DC Transformer Power Supply 120 VAC-to-12VDC (500 mA max) Power Supply 12VDCT			✓		✓	
Power-Out Alert™ PS-110 Power Outage Detector	✓	✓				