



## Main

|                           |                 |
|---------------------------|-----------------|
| Range                     | PowerPact       |
| Product name              | PowerPact L     |
| Device short name         | L-Frame         |
| Product or Component Type | Circuit breaker |
| Device Application        | Distribution    |

## Complementary

|  |   |
|--|---|
| Line Rated Current                     | 600 A   |
| Number of Poles                        | 3P  |
| Control Type                           | Toggle  |
| Breaking capacity code                 | D   |
| Breaking capacity                      | 25 KA 240 V AC 50/60 Hz UL 489<br>18 KA 480 V AC 50/60 Hz UL 489<br>14 KA 600 V AC 50/60 Hz UL 489<br>20 kA 250 V DC UL 489   |
| [Ue] rated operational voltage         | 600 V AC 50/60 Hz IEC 60947-3   |
| Network Frequency                      | 50/60 Hz  |
| [Ics] rated service breaking capacity  | 25 KA 220/240 V AC 50/60 Hz IEC 60947-2<br>18 KA 380/440/415 V AC 50/60 Hz IEC 60947-2<br>14 KA 500/525 V AC 50/60 Hz IEC 60947-2<br>20 KA 250 V DC IEC 60947-2<br>20 kA 500 V DC IEC 60947-2 |
| [Uimp] rated impulse withstand voltage | 8 kV IEC 60947-2  |
| Trip unit technology                   | Electronic, standard, Micrologic 3.2, LI  |
| Continuous current rating              | 80 %  |
| [Ui] rated insulation voltage          | 750 V IEC 60947-2   |
| Trip unit name                         | Micrologic 3.2  |
| Suitability for isolation              | Yes conforming to IEC 60947-2   |
| Utilisation category                   | Category A  |
| AWG gauge                              | 2 x AWG 2/0...500 kcmil aluminium/copper  |
| Local signalling                       | Ready 1 LED green)<br>Alarm 1 LED 90 % Ir orange)<br>Alarm LED 105 % Ir red)<br>Switched off (OFF) 1 trip indicator green)  |
| Mounting mode                          | Unit mount (lug)  |
| Mounting Support                       | Lug   |
| Electrical connection                  | Lugs line<br>Lugs load  |
| Terminal identifier                    | AL600LS52K3   |
| Long time pick-up adjustment range     | 0.25...1 x In   |
| Tightening torque                      | 442.54 lbf.in (50 N.m) 0.11...0.37 in <sup>2</sup> (70...240 mm <sup>2</sup> ) (2 x AWG 2/0...500 kcmil)  |

|                             |  |
|-----------------------------|--|
| Number of slots             | 2 auxiliary switch OF plug-in<br>1 alarm switch SD plug-in<br>1 overcurrent trip switch SDE plug-in<br>1 voltage release MN or MX plug-in) |
| Power wire stripping length | 1.22 in (31 mm)<br>2.40 in (61 mm)   |
| Color                       | Black  |
| Height                      | 13.39 in (340 mm)  |
| Width                       | 5.51 in (140 mm)   |
| Depth                       | 4.33 in (110 mm)   |
| Product Weight              | 13.67 lb(US) (6.2 kg)  |
| Communication interface     | Modbus<br>Ethernet   |

## Environment

|                                       |   |
|---------------------------------------|---|
| Standards                             | UL<br>CSA<br>NEMA<br>NOM-003-SCFI-2000<br>IEC 60947-2 |
| Product certifications                | UL<br>CSA<br>NOM                                      |
| IP degree of protection               | Front cover IP40                                      |
| Pollution degree                      | 3 conforming to IEC 60947-1                           |
| Ambient Air Temperature for Operation | 28...158 °F (-2...70 °C)                              |
| Ambient Air Temperature for Storage   | -58...185 °F (-50...85 °C)                            |
| Operating altitude                    | < 2000 m without derating<br>5000 m with derating     |

## Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 01116 - L ELEC TRIP UNIT MOUNT BREAKER/SW |
| Discount Schedule     | DE2                                       |
| GTIN                  | 785901626701                              |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 17.10 lb(US) (7.756 kg)                   |
| Returnability         | Yes                                       |
| Country of origin     | US  |

## Packing Units

|                        |                     |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE                 |
| Package 1 Height       | 9.50 in (24.13 cm)  |
| Package 1 width        | 11.50 in (29.21 cm) |
| Package 1 Length       | 20.00 in (50.8 cm)  |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |

---

|                     |   |
|---------------------|---|
| Circularity Profile | <a href="#">End Of Life Information</a> |
| PVC free            | Yes                                     |

---

**Contractual warranty**

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---