

# HOM120EPD

Mini circuit breaker, Homeline, 20A, 1 pole, 120 VAC, 10 kA AIR, ground fault class B, plug in mount



## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A
Certifications	UL Listed
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Ground fault protecting class B 30 mA
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	AWG 14...AWG 8 aluminium/copper)1

## Complementary

Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 8)
-------------------	--

## Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	00143 - HOM 1 & 2P EPD BREAKERS
Discount Schedule	DE3D
GTIN	00785901636502
Nbr. of units in pkg.	1
Package weight(Lbs)	0.61 lb(US) (0.28 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	1.30 in (3.302 cm)
Package 1 width	3.90 in (9.906 cm)
Package 1 Length	5.50 in (13.970 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Halogen content performance	Halogen free product

---

### Contractual warranty

---

Warranty	Lifetime
----------	----------

---