

8501CO22V20

Power Relay, Type C, 10A resistive at 110 VDC, DPDT, 2 normally open and 2 normally closed contact, 120 VAC coil



Main

Product range	Power Relay 8501C
Product type	Power relay
Short name	Type C
[In] rated line current	20 A
Device application	Suited for controlling small single phase motors and other light loads
Switch function	DPDT
Contact composition	2 NO/2 NC
[Uc] control circuit voltage	120 V AC 50/60 Hz
Maximum switching voltage	325 V DC

Complementary

Class number	8501
Phase	1 phase
Terminal connects	Screw clamp terminal
Wire range	AWG 10 copper
Terminal tightening torque	11...15 lbf.in (1.24...1.69 N.m)
Coil burden	10 VA
Mounting	Panel mounting

Environment

Ambient temperature range - operational	-22...122 °F (-30...50 °C)
Product certifications	UL listed file E78351 CCN NLDX CSA CE
Height	3.12 in (79.25 mm)
Width	2.5 in (63.50 mm)
Depth	2.53 in (64.26 mm)

Ordering and shipping details

Category	21131 - 8501 C
Discount Schedule	CP2
GTIN	00785901052241
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7 lb(US) (0.32 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Package 1 Height	2.40 in (6.096 cm)
Package 1 width	2.50 in (6.350 cm)
Package 1 Length	3.20 in (8.128 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------