

## Product data sheet

### Characteristics

# MPL32225

MP Meter Pak, meter center, two ringless sockets, lever bypass, 5th jaw, OH, UG, 350 A bus, 225 A, 240 VAC single phase 3W



### Main

Product	Meter Center
Socket Rating	225 A
Main Type	Main Lugs
Number of Jaws	5
Number of Meter Sockets	2
Socket Type	Ringless

### Complementary

Main Rating	350 A
Bus Rating	350 A
Certifications	UL Listed
Type	Meter-Pak
Busbar Material	Aluminium busbar
Bypass Type	Lever bypass
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	240 V AC
Mounting	Surface
Phase	1 phase
Service Feed Location	OH UG
Wire Size	AWG 1/0...600 kcmil 1 aluminium AWG 1/0...600 kcmil 1 copper
Wire Configuration	3-wire
Height	60.25 in (1530.35 mm)
Width	19.43 in (493.52 mm)
Depth	9.62 in (244.35 mm)

### Ordering and shipping details

Category	00021 - METER-PAK
Discount Schedule	DE4
GTIN	00785901299622
Nbr. of units in pkg.	1
Package weight(Lbs)	110 lb(US) (49.90 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	0.93 ft (0.284 m)
Package 1 width	1.67 ft (0.508 m)
Package 1 Length	5.10 ft (1.554 m)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------