



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Number of Poles	3P
Breaking capacity code	G
Magnetic tripping current	1000...2000 A
Electrical connection	Lugs load Lugs line
Terminal identifier	AL400L61K4
Tightening torque	442.54 Lbf.in (50 N.m) 0.05...0.37 in ² (35...240 mm ²) (AWG 2...500 kcmil) 442.54 lbf.in (50 N.m) 0.05...0.47 in ² (35...300 mm ²) (AWG 2...600 kcmil)
Height	13.39 in (340.11 mm)
Width	7.27 in (184.66 mm)
Depth	6.61 in (167.89 mm)

Ordering and shipping details

Category	01116 - L ELEC TRIP UNIT MOUNT BREAKER/SW
Discount Schedule	DE2
GTIN	00785901942856
Nbr. of units in pkg.	1
Package weight(Lbs)	25.5 lb(US) (11.57 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	13.44 in (34.131 cm)
Package 1 width	7.38 in (18.733 cm)
Package 1 Length	31.44 in (79.851 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------