

# HOM48L125GC

Load center, Homeline, 1 phase, 4 spaces, 8 circuits, 125A fixed main lugs, NEMA1, gnd bar, combo cover



## Main

Product Type	Load Center
Marketing Trade Name	Homeline
Load Center Type	Main lugs
Rated Current	125 A
Number of Spaces	4
Maximum Number of Single Pole Circuits	8
Enclosure Rating	NEMA 1 for indoor NEMA 3R for outdoor
Cover Type	Combination flush/surface cover
Electrical Connection	Lugs
Provided Equipment	Grounding bar 1)

## Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number of Tandem Breakers	4
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 14...AWG 2/0 copper AWG 12...AWG 2/0 aluminium AWG 4...250 kcmil copper AWG 4...300 kcmil aluminium
Ground Bar	Grounding bar included (not installed)
Wiring Configuration	3-wire
Busbar Material	Tin plated aluminium busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel grey
Box Number	21
Height	14.80 in (376 mm)
Depth	3.82 in (97 mm)
Width	8.90 in (226 mm)

## Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL listed file E-6294

## Ordering and shipping details

Category	00149 - HOM 2-8 CKT,MLO,NEMA1&3R
Discount Schedule	DE3C
GTIN	00785901484363
Nbr. of units in pkg.	1
Package weight(Lbs)	9.58 lb(US) (4.35 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.30 in (10.922 cm)
Package 1 width	10.50 in (26.67 cm)
Package 1 Length	16.60 in (42.164 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	72
Package 2 Weight	732.00 lb(US) (332.029 kg)
Package 2 Height	38.20 in (97.028 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	Lifetime
----------	----------