



Main

Range of product	Harmony 9001SK
Product or component type	Push-button
Device short name	9001SK
Bezel material	Black plastic

Complementary

Mounting diameter	1.18 in (30 mm)
Shape of signaling unit head	Octagonal
Light block supply	Full voltage 24 V Full voltage 28 V
Contacts type and composition	Without contact block
Product certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE
IP degree of protection	IP64
NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13


Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901040453
Nbr. of units in pkg.	1
Package weight(Lbs)	0.4 lb(US) (0.18 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	5.08 in (12.903 cm)
Package 1 width	2.00 in (5.080 cm)
Package 1 Length	12.90 in (32.774 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------